



MASTERColour CDM-TC Fresh

MASTERColour CDM-TC Fresh 70W/740 G8.5

Single-ended, high-efficiency Ceramic Metal Halide discharge lamp with special color enhancement properties

Product data

• General Characteristics

Cap-Base	G8.5
Bulb	T14 [T 14 mm]
Bulb Finish	Clear
Operating Position	any [Any or Universal (U)]
Life to 5% failures EL	9000 hr
Life to 10% failures EL	10000 hr
Life to 20% failures EL	12000 hr
Life to 50% failures EL	15000 hr

• Light Technical Characteristics

Color Code	740 [CCT of 4000K]
Color Rendering Index	67 (min), 70 (nom) Ra8
Color Designation (text)	Cool White
Color Temperature	4000 K
Color Temperature Technical	3900 K
Luminous Flux Lamp EL	6000 Lm
Luminous Efficacy Lamp EL	82 Lm/W
Lumen Maintenance EL 2000h	92 %
Lumen Maintenance EL 12000h	79 %
Design Mean Lumens EL	6000 Lm
Chromaticity Coordinate X	0.386 -
Chromaticity Coordinate Y	0.385 -

• Electrical Characteristics

System Power EL	80 W
Lamp Wattage	70 W
Lamp Wattage EL 25°C, Rated	73.0 W
Lamp Wattage EL 25°C, Nominal	70.0 W
Lamp Voltage	83 V
Lamp Current EL	0.875 A
Ignition Time	30 (max) s
Run-up time 90%	3 (max) min
Re-ignition Time [min]	15 (max) min
Dimmable	No

• Environmental Characteristics

Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content	6 mg
Energy consumption kWh/1000h	80 kWh

• UV-related Characteristics

Damage Factor D/fc PET (NIOSH)	0.4 (max) - 8 (min) h500lx
--------------------------------	----------------------------

• Luminaire Design Requirements

Pinch Temperature	300 (max) C
Bulb Temperature	550 (max) C

PHILIPS

MASTERColour CDM-TC Fresh

• Product Dimensions

Overall Length C	85 (max) mm
Diameter D	15 (max) mm
Light Center Length L	51 (min), 52 (nom), 53 (max) mm
Arc Length O	7.15 mm
Light Center Length L [inch]	2 (min), 2.45 (nom), 2.9 (max) in
Overall Length C [inch]	3.3 (max) in
Diameter D [inch]	0.6 (max) in

• Product Data

Order code	928196705131
Full product code	928196705131


Full product name	MASTERColour CDM-TC Fresh 70W/740 G8.5
Order product name	MASTERColour CDM-TC Fresh 70W/740 G8.5
Pieces per pack	1
Packing configuration	12
Packs per outerbox	12
Bar code on pack - EAN1	8718291163299
Bar code on outerbox - EAN3	8718291163305
Logistic code(s) - 12NC	928196705131
ILCOS code	MT/UB-70/740-H-G8.5-17/85
Net weight per piece	0.010 kg

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures


- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)

Dimensional drawing




MASTERColour CDM-TC Fresh 70W/740 G8.5

Product	C (Max)	D (Max)	L (Min)	L (Norm)	L (Max)	O (Norm)
CDM-TC ACCENT 70W/740 G8.5	85	15	51	52	53	7.15



G8.5

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 10
data subject to change