



Ecoclick Starters

S16 70-125W 240V UNP/20X10CT

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

Product data

General information	
System Description	Single
Operating and electrical	
Power (Nom)	70 125 W
Pulse Voltage (Min)	900 V
Non Reclosure Voltage (Min)	170 V
Voltage (Nom)	240 V
System characteristics	
Capacitor	Yes
Mechanical and housing	
Housing Color	White

Cap-Base Information	
	2 Pins
Product data	
Full product code	871150090356331
Order product name	S16 70-125W 240V UNP/20X10CT
EAN/UPC - Product	8711500903563
Order code	928390930371
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	200
Material Nr. (12NC)	928390930371
Net Weight (Piece)	7.000 g

Ecoclick Starters

Dimensional drawing

F

Product	C (max)	E (max)
S16 70-125W 240V UNP/20X10CT	40.3 mm	21.5 mm

S16 70-125W 240V UNP/20X10CT

