

ECOSYN®-DRILL / ECOSYN®-MRX

Self-drilling with high drilling performance — also in stainless steel

Direct screwing fasteners for aluminium, steel plates and corrosion resistant thin-wall sheets in a single operation. Secure, fast, multifunctional and cost-effective.








	Order number	Brand	Details	Materials	Surface	Ø from/up to
	BN 1878	ecosyn®-drill	Phillips pan head self-drilling screws type N, form H	Steel case hardened 560 HV	zinc plated blue	ST2.9 – ST6.3
	BN 11904	ecosyn®-drill	Octagon (8 Lobe) pan head self-drilling screws, type N	Steel case hardened 560 HV	zinc plated blue	ST3.5 – ST4.8
	BN 1879	ecosyn®-drill	Phillips flat countersunk head self-drilling screws form H, type P	Steel case hardened 560 HV	zinc plated blue	ST2.9 – ST6.3
	BN 1880	ecosyn®-drill	Hex head self-drilling screws form K	Steel case hardened 560 HV	zinc plated blue	ST3.5 – ST6.3
	BN 1387	ecosyn®-MRX	Octagon (8 Lobe) pan head self-drilling screws with flange	Stainless steel	–	ST4.2 – ST4.8
	BN 10319	ecosyn®-MRX	Hex head self-drilling screws with sealing ring	Stainless steel	–	ST4.8 – ST6.3
	BN 14729	ecosyn®-MRX	Hex head self-drilling screws without sealing ring	Stainless steel	–	ST4.2 – ST6.3
	BN 14727	ecosyn®-MRX	Pozi pan head self-drilling screws form Z	Stainless steel	–	ST3.5 – ST4.8

All ecosyn®-drill and ecosyn®-MRX products are available from the Bossard E-Shop.

INNOVATION

Amazingly simple fastenings

These product solutions open up new perspectives for construction and design. The result: lean designs, simplified operations, reliable assembly, increased productivity.

	Order number	Details	Materials	Surface	Ø from/up to
	BN 1206	Hex socket head cap screws with special low head	~ 010.9	black	M2– M10
	BN 9524	Hexalobular (6 Lobe) socket flat head screws with special low head, fully threaded	– 08.8	zinc plated blue	M2– M10
	BN 20146	Hexalobular (6 Lobe) socket head cap screws with extremely low head, fully threaded	Stainless steel A2	–	M2 – M8
	BN 1720	Phillips pan head assembled (SEMs) screws form H, with captive spring lock washer DIN 127 B	Steel 4.8 Helical spring: spring steel	zinc plated blue	M2.5 – M5
	BN 40100	Phillips cross recessed cheese head screws with captive tooth lock washer ~DIN 6797 A	Steel 4.8 Tooth lock washer: spring steel	zinc plated blue	M3; M3.5; M4
	BN 20218	Pozi pan head screws «Freedriv» with slot and captive square flex washer	Steel 5.8	zinc plated blue	M3; M3.5; M4
	BN 14551	Hexalobular (6 Lobe) socket pan head thread forming screws with slot and ribs, metric thread	Steel case hardened 450 – 550 HV	zinc plated blue waxed	M3; M4

You will find a wide range of innovative product solutions in the Bossard E-Shop.