

GN 135 | Two-way connecting clamps

Aluminium



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

MATERIAL

Aluminium, matte finish.
AISI 304 stainless steel screws and nuts.

STANDARD EXECUTIONS


- **GN 135-BL**: natural aluminium.
- **GN 135-SW**: epoxy resin coating, RAL 9005 black colour.

FEATURES AND APPLICATIONS


The assembly holes of GN 135 connecting clamps allow an excellent match with tubes GN 990 (see page 1778).

Within the same nominal size the connecting clamp may be supplied with the holes d_1 and d_2 , square holes s_1 and s_2 or in combination with round and square holes of unequal dimensions.

The clamping screw d_3 may be replaced by clamping kit GN 911 (see page 1782).



GN 911



Code BL	Code SW	Description	Round hole (B) d_1	Round hole (B) d_2	Square hole (V) s_1	Square hole (V) s_2	d_3	d_4	d_3 Clamping kit	d_4 Clamping kit	
GN.44557	GN.44558	GN 135-B30-B40-60-2-*	30	40	-	-	M8	M10	GN 911-M8-55	GN 911-M10-55	500
GN.44559	GN.44560	GN 135-B30-B48-60-2-*	30	48	-	-	M8	M10	GN 911-M8-55	GN 911-M10-55	486
GN.44561	GN.44562	GN 135-B30-B50-60-2-*	30	50	-	-	M8	M10	GN 911-M8-55	GN 911-M10-55	479
GN.44569	GN.44570	GN 135-B40-B48-60-2-*	40	48	-	-	M8	M10	GN 911-M8-55	GN 911-M10-55	461
GN.44571	GN.44572	GN 135-B40-B50-60-2-*	40	50	-	-	M8	M10	GN 911-M8-55	GN 911-M10-55	454
GN.44564	GN.44565	GN 135-B30-V40-60-2-*	30	-	-	40	M8	M10	GN 911-M8-55	GN 911-M10-55	900
GN.44566	GN.44567	GN 135-B30-V50-60-2-*	30	-	-	50	M8	M10	GN 911-M8-55	GN 911-M10-55	599
GN.44574	GN.44575	GN 135-B40-V50-60-2-*	40	-	-	50	M8	M10	GN 911-M8-55	GN 911-M10-55	800
GN.44586	GN.44587	GN 135-V30-V40-60-2-*	-	-	30	40	M8	M10	GN 911-M8-55	GN 911-M10-55	900
GN.44588	GN.44589	GN 135-V30-V50-60-2-*	-	-	30	50	M8	M10	GN 911-M8-55	GN 911-M10-55	750
GN.44596	GN.44597	GN 135-V40-V50-60-2-*	-	-	40	50	M8	M10	GN 911-M8-55	GN 911-M10-55	750
GN.44579	GN.44580	GN 135-V30-B40-60-2-*	-	40	30	-	M8	M10	GN 911-M8-55	GN 911-M10-55	600
GN.44581	GN.44582	GN 135-V30-B48-60-2-*	-	48	30	-	M8	M10	GN 911-M8-55	GN 911-M10-55	479
GN.44583	GN.44584	GN 135-V30-B50-60-2-*	-	50	30	-	M8	M10	GN 911-M8-55	GN 911-M10-55	450
GN.44591	GN.44592	GN 135-V40-B48-60-2-*	-	48	40	-	M8	M10	GN 911-M8-55	GN 911-M10-55	447
GN.44593	GN.44594	GN 135-V40-B50-60-2-*	-	50	40	-	M8	M10	GN 911-M8-55	GN 911-M10-55	830

* Complete the description of the standard item needed by adding the finish of the connector clamps: BL (blank) or SW (black).