

Product type designation

Product description

PB BFOC Plug PCF

BFOC screw-connector for PCF-fibre optic cable with plastic Cladding
BFOC PLUG PCF ON-SITE MOUNTING ON PCF FO CABLES;
PACK OF 20PCS + CLEANING CLOTHS



Figure similar

Suitability for use

For connection of PCF fiber-optic cables

Transmission rate

Transfer rate / with PROFIBUS

9.6 kbit/s ... 12 Mbit/s

Interfaces

Number of optical interfaces / for fiber optic cable

1

Design of the optical interface / for network components or terminal equipment

BFOC connector

Type of electrical connection / FastConnect

No

Mechanical data

Material / of the enclosure

Metal and plastic

Design, dimensions and weight

Type of cable outlet

180° cable outlet

Width

10 mm

Height

10 mm

Depth

10 mm

Net weight

8 g

Permitted ambient conditions

Protection class IP

IP20

Product properties, functions, components / general

Product property

- silicon-free

Yes

Product component

- strain relief

Yes

Standards, specifications, approvals

Certificate of suitability

- RoHS conformity
- UL approval
- Railway application in accordance with EN 50155

Yes

No

No

Further Information / Internet Links

Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09.03.2015