



Lockmakers Since 1780

CP Range of padlocks

All-weather, recodable combination padlocks



CP60 Range
60mm - 5 Wheel



CP50 Range
50mm - 4 Wheel



CP40 Range
40mm - 4 Wheel

Toughness guaranteed.



**10 Year
Guarantee**




Lockmakers Since 1780

A heavy-duty range of recodable combination padlocks

CP Range - Features

- Hardened steel shackle (Rustproof versions stainless steel shackles)
- Double locking
- CP40 and CP50 - 4 Wheels 10,000 combinations
- CP60 - 5 Wheels 100,000 combinations
- Fully recodable
- Die cast alloy body with dual compound cover
- Patented



Can be coded alike



No keys to lose



All Weather



Rustproof versions available



100,000 combinations
CP60



10,000 combinations
CP50 and CP40




1,000 combinations
CP30

Unique in design, our combination locks are manufactured to the highest standards for quality performance. Easy to use, they are fully recodable and a number of locks can be coded alike so that one code opens several locks. Many of our locks are patented and have individual design features to improve performance and security.

Uses

Sheds, cupboards, storage areas, cabinets, lockers





CP60 - 60mm padlock
5 wheels
100,000 combinations



CP50 - 50mm padlock
4 wheels
10,000 combinations



CP40 - 40mm padlock
4 wheels
10,000 combinations



CP30 - 30mm padlock
3 wheels
1,000 combinations




CP50S and CP40S -
50mm and 40mm padlocks
4 wheels
10,000 combinations
Rustproof - Stainless steel shackles





SQUIRE

Lockmakers Since 1780



Model Number	Category	Security Rating	Shackle Material	Body Material	Dimensions (mm)					Mechanism	No. of Wheels	No. of Combinations	Barcode Number	Packaging
					A	B	C	D	E					
CP60	@HOME	6	Hardened Steel	Die cast alloy	60	33	10	34	28	Recodable Combination	5	100,000	5012245025736	Blister
CP60/2.5	@HOME	6	Hardened Steel	Die cast alloy	60	33	10	63	28	Recodable Combination	5	100,000	5012245025743	Blister
CP60CS	@HOME	7	Hardened Steel	Die cast alloy	60	33	10	29	22	Recodable Combination	5	100,000	5012245025750	Blister
CP50	@HOME	5	Hardened Steel	Die cast alloy	50	26	8	26	22.6	Recodable Combination	4	10,000	5012245021783	Blister
CP50/1.5	@HOME	5	Hardened Steel	Die cast alloy	50	26	8	38.1	22.6	Recodable Combination	4	10,000	5012245021806	Blister
CP50/2.5	@HOME	5	Hardened Steel	Die cast alloy	50	26	8	63.5	22.6	Recodable Combination	4	10,000	5012245021813	Blister
CP50CS	@HOME	6	Hardened Steel	Die cast alloy	50	26	8	22	16	Recodable Combination	4	10,000	5012245021790	Blister
CP40	@HOME	4	Hardened Steel	Die cast alloy	40	22	6	20	17	Recodable Combination	4	10,000	5012245024609	Blister
CP40/2.5	@HOME	4	Hardened Steel	Die cast alloy	40	22	6	63	17	Recodable Combination	4	10,000	5012245024616	Blister
CP40CS	@HOME	4	Hardened Steel	Die cast alloy	40	22	6	17	13	Recodable Combination	4	10,000	5012245024623	Blister
CP30	@HOME	2	Hardened Steel	Die cast alloy	30	16	4	15	13	Recodable Combination	3	1,000	5012245033649	Blister
CP50S	@LEISURE	4	Stainless Steel	Die cast alloy	50	26	8	26	22.6	Recodable Combination	4	10,000	5012245029659	Blister
CP40S	@LEISURE	3	Stainless Steel	Die cast alloy	40	22	6	20	17	Recodable Combination	4	10,000	5012245029642	Blister
RK/CP40/CP50	@HOME	na	na	na	na	na	na	na	na	na	na	na	Special	BAG
RK/SS50COMBI /CP60	@HOME	na	na	na	na	na	na	na	na	na	na	na	Special	BAG