

Line laser, red, 650 nm, 90 °, 20 mW

LH650-20-24(20x80)-F1600-M12
Order Number: 70126891

Main Parameters (*)	min	typ	max	Unit
Wavelength		650		nm
Optical Output Power		20		mW
Operating Voltage	21.6	24	26.4	V DC
Operating Current	10	40	70	mA
Operating Temperature	-20		50	°C
Storage Temperature	-40		80	°C

Main Data

Warranty 1 years

Technical Parameters

Lifetime > 10,000 h
RoHS yes

Optical Parameters

Beam Shape	Line
Laser Class	2M
Divergence	H - 1.0 mrad
Fan Angle	90 °
Line Thickness	<1.5mm@1.6m
Operating Distance	1.6 m
Optics	glass lens AR coated
Laser technology	Single Mode Diode
Protection Lens	yes
Focus	fixed (1600mm)

Electrical Parameters

Potential of Housing	isolated
Connector	CON-M12

Mechanical Parameters

Size	Ø20x80 mm
Material	aluminium
Output Aperture	5.5 mm
Housing Color	black
Weight	63 g
Protection Class	IP 64


(*) Over the complete operating temperature range

Features




- Operating Voltage 24V DC
- Isolated housing
- Laser Class 2M
- Small laser head
- Protection lens

Picture



Safety Label



Valid Revision

| 23-JAN-2020