

Item code

CDMD 1.5



Brief description:

10A CD contacts, gold plated, 1,50mm², AWG 16

Product description

Model	male contacts
Version	Crimp contacts CLASS series
Series	10A CD contacts
Family	crimp contacts
N° of poles	1 pole

Technical data

Current	10 A
Wire section	1,50 mm ²
AWG size	16
Operating temperature range (min, max)	-40°C ... +125°C
Contact type	gold plated

Other technical details

Weight	0,80 g
---------------	--------

Approvals / Standards

Quality mark	 , EAC
Conformity	CQC, CE

General ordering information

EAN code	8015747015646
Tariff number	85369095

Packaging Information

Packaging length	112,00 mm
Packaging height	95,00 mm
Packaging width	117,00 mm
Packaging weight	1,28 kg
Packaging volume	1,24 dm ³
Packaging description	Carton box
Packaging quantity	1600 Pcs
Packaging EAN code	8015747207010
Sub-packaging length	50,00 mm
Sub-packaging height	44,00 mm
Sub-packaging width	50,00 mm
Sub-packaging weight	0,16 kg
Sub-packaging volume	0,11 dm ³
Sub-packaging description	Plastic box
Sub-packaging quantity	200 Pcs
Sub-packaging EAN barcode	8015747015653



Item code

CDMD 1.5



Catalogue drawings

CDM



CDF

