

**TEMPO TAM131308**



**Order symbol:** TAM131308  
**Product nbr:** 5814023  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074011459  
**EI. number:**  
 Finland: 3438266  
 Electric No. Denmark: 8212045282  
 Electric No. Sweden: 5814023

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

**Dimensions: Length Width Height Accessories:**

<b>mm:</b>	130	130	75	MIV 10	DIN-35 Mounting rail
<b>inch:</b>	5.1	5.1	3.0	MP 1313	Mounting plate
				FP 10674	

**Materials: DPS 14553 Grey sealing plug set**

<b>Material:</b> ABS	<b>Rating:</b>
<b>Base colour:</b> RAL 7035 -light grey	Ingress Protection (EN 60529): IP65
<b>Cover screws material:</b> Polyamide	Impact Resistance (EN 62262): IK07
<b>Cover colour:</b> RAL 7035 -light grey	Electrical insulation: Totally insulated
<b>Cover screws colour:</b> Grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Gasket material:</b> Polyurethane	Flammability Rating: UL 94 HB
	Glow Wire Test (IEC 695-2-1) °C: 650

**Temperatures: Certificates: SGS Fimko**

<b>Temperature °C (short term):</b> -40 ... 80 °C
<b>Temperature °C (continuous):</b> -40 ... 60 °C
<b>Temperature °F (short term):</b> -40 ... 175 °F
<b>Temperature °F (continuous):</b> -40 ... 140 °F

**Accessories: DRM 100 DIN-15 Mounting rail**

DRM 100	DIN-15 Mounting rail
---------	----------------------

