


THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS



**SPECIFICHE DI CARICO:**

Componente spessore 4,0 mm forza F=20N min  
 Componente spessore 4,5 mm forza F=25N min  
 Componente spessore 5,0 mm forza F=30N min

**CHARGE SPECIFICATIONS:**

Thickness Component 4,0 mm force F=20N min:  
 Thickness Component 4,5 mm force F=25N min  
 Thickness Component 5,0 mm force F=30N min



**AAVID THERMALLOY**  
 EUROPE [www.aavidthermalloy.com](http://www.aavidthermalloy.com)

Via del Fonditore, 4  
 zona Industriale Roveri  
 40138 Bologna ITALY  
 Tel. +39 051 764011  
 Fax +39 051 764090

COMPANY  
 WITH QUALITY SYSTEM  
 CERTIFIED BY LISA  
 ISO 9001:2000

Die n.	MATERIAL EN10132-4 C67S 0.35 x 4							DRAWING n.	439647		
Factor	GENERAL TOLERANCES							Vis. n.			
Perim.								Description:	5901G Spring clip		
Area mm <sup>2</sup>	FINISH See note							EDN			
Weight		C	11May16	Cancel quotes not necessary/cancellate quote non necessarie				IF			
Note:	Zincatura bianca alta resistenza\ Zn high resistance plated Tratt.termico\thermal treatment: BONFICA 42-46 HRC all dimensions in mm	Drawn	B	190ct11	Confirm drawing			SE			
		Check	A	25Sep07	ORIGINAL (was ZA3899)			By	Format	Scale	1
REV	Date	Revision description						A4	1 : 1		