

## Product information

# 25 03 125

## Snipe Nose Side Cutting Pliers (Radio Pliers)

DIN ISO 5745

- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 61 HRC
- Straight jaws
- Vanadium electric steel, forged, multi stage oil-hardened



### General

Article No.	25 03 125
EAN	4003773043065
Pliers	chrome-plated
Head	chrome-plated
Handles	plastic coated
Weight	72 g
Dimensions	125 x 54 x 12 mm
Standard	DIN ISO 5745
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 2.2 mm
Cutting capacities hard wire (diameter)	Ø 1.6 mm
Jaw thickness (joint) (T1)	7.0 mm
Tips width (W4)	2.5 mm
Tips thickness (T2)	1.8 mm
Jaw length (L3)	27.0 mm
Head width (W3)	13 mm

## Technical details



*technical change and errors excepted*