

## Product information

# 34 12 130

## Precision Electronics Gripping Pliers

DIN ISO 9655




- For very precise assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Smoothly ground gripping surfaces, edges finely rounded
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Flat, wide jaws
- Ball bearing chrome steel, forged, multi stage oil-hardened



General	
Article No.	34 12 130
EAN	4003773061458
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	61 g
Dimensions	135 x 62 x 19 mm
Standard	DIN ISO 9655
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Jaw length (B)	21.9 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	1.4 mm
Tips thickness (F)	3.5 mm
Head width (A)	11.2 mm



technical change and errors excepted

