


Category (ETIM):	Device mounts
Type:	Device mount IP20-SDGLK LED
Order number:	18234504100
Configuration:	Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Operating device:	Electronic driver (1 pcs.)
System performance (W):	47
Luminaire luminous flux (lm):	7000
lm/W:	153
Ambient temperatures:	10°C / 35°C
Certifications:	IP 20, protection class I, F, DIN10500/Food, Indoor, CE
Colour of the housing:	traffic white RAL 9016
Weight (net) (kg):	2
Dimensions LxWxH/DxH (mm):	1531 x 63 x 54
mounting method:	Mounting rail system mounting
EAN-number:	4020863336210
Commodity code:	94051098


SDGLK LED 7000lm 840 • vw • ED • 18234504100



Lighting technology
Diffuser, frosted-direct/indirect distribution
SDGLK LED 7000 lm 840



η_{LB}	100 %
lm/W	153
$\Phi \downarrow/\uparrow$	84 % / 16 %
UGR q/l	25.2 / 23.8



Quick-fit mounting system Device mounts; Device mount made of galvanised, profiled sheet steel, surface coated with polyester resin enamel. Toolless fastening with two integrated lateral lever locks. LED unit in housing length for optically seamless light run. Housing colour traffic white RAL 9016; Direct/indirect light distribution, frosted diffuser made of PMMA plastic with inner longitudinal prisms. Optically seamless light run. Heat-resistant cables including fixed 3-pole rapid installation plug connector with tool-less phase pre-selection and locating finger.

Dimensions LxWxH/DxH (mm): 1531 x 63 x 54
Configuration: Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Luminaire luminous flux (lm): 7000
lm/W: 153
Operating device: Electronic driver (1 pcs.)
System performance (W): 47
Conditions: Suitable for use in ambient temperatures of 10°C to 35°C
Certifications: IP 20, protection class I, F, DIN10500/Food, Indoor, CE

Regiolux GmbH
Type: SDGLK LED 7000 840 ET vw
Article number: 18234504100
Product deep link: <http://www.regiolux.de/de/article/18234504100>
5 year guarantee after registration on website.