

coolant nozzle DriveKD

For rotary tools

RIHETEC
Kühlmitteldosen

Application:

Conventional coolant nozzles, often spray in all directions and do not provide a direct coolant jet. This often results in inadequate cooling at the tool cutting edge. The DriveKD performs its task superbly well.

Execution:

- threaded connectors M8x1, M10x1 and 1/8 thread
- internal pipe diameter 4 mm
- pipe length 50 mm or 70 mm
- max. pressure 10 bar (50 mm, 70 mm)
- special length of 100 mm available upon request (max. pressure up to 6 bar)

Advantage:

- quick, easy installation
- Precise and strong coolant stream onto the tool cutting edge, for a long service life.
- precisely adjust the coolant stream using the flexible pipe
- reasonable price
- Broad range of uses



Art. no.	21665 256
Brand	RIHETEC
Manufacturer Part Number	07G18
Gross Weight	0.019 kg
Product Group	278

EAN

4260711110153