

High-pressure hose

Accessories for cylinders and pumps



Application:

For connecting hydraulic systems.

Execution:

- Max. operating pressure 700 bar.
- Pressed-on rubber strain relief for long service life and durability.
- Four-layer design including two sturdy layers of mesh wire
- External layer made of polyurethane for enhanced resistance against wear caused by friction.

Delivery:

1x high-pressure hose, 3/8 inch-18 NPT, 720 bar, length 600 mm, for HP hydraulics.



Art. no.	29730 400
Brand	ENERPAC
Manufacturer Part Number	HC 7206C
Hose length	1800 mm
Two-sided connection thread	NPT 3/8 inch x 18 mm
Min. bending radius	70 mm
Nominal width	6 mm
Internal diameter	6.4 mm
Dynamic operating pressure	720 bar
Gross Weight	1.181 kg
Product Group	269