

## Cordless inspection camera

M12IC-201C(S)



### Execution:

- 270° rotating display
- 68.6 mm/2.7 inch colour LCD display
- Waterproof 9 mm camera head with a resolution of 640 x 480 pixels
- 3-stage LED light for optimal illumination
- Flexible, waterproof 9.14 mm camera cable
- The rechargeable REDLITHIUM™ battery offers a perfectly adapted design, advanced electronics and zero-loss power output for a longer operating time and service life than previous models



<b>Art. no.</b>	<b>70700 740</b>
<b>Brand</b>	MILWAUKEE
<b>Manufacturer Part Number</b>	4933441680
<b>Model</b>	M12IC-201C(S)
<b>Battery included</b>	Yes
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	M12 B2
<b>Rechargeable battery/battery capacity</b>	2 Ah
<b>Battery voltage</b>	12 V/AC
<b>Type of rechargeable battery/battery</b>	Li-Ion
<b>Display (diagonal)</b>	68.6 mm
<b>Cable length</b>	9.14 mm
<b>Included in delivery</b>	Attachable tools (hooks, mirrors and magnets) included in scope of delivery 1 x 12 V/2 Ah Red Li-ion rechargeable battery, quick charger C12 C, attachable accessories (hooks, mirrors and magnets), transport case
<b>Weight</b>	0.66 kg
<b>Gross Weight</b>	2.970 kg
<b>Product Group</b>	7MA

### EAN

4002395001910