

Oval-Head Phillips Screws

Features

- No burrs and sharp edges
- Screw material: A2 stainless steel
- Passivated finish
- Material and finish comply with 211/65/EU (RoHS)
- Meets ISO 7985 standard

Length	L
3	2.8~3.2
4	3.75~4.25
5	4.75~5.25
6	5.75~6.25
8	7.70~8.30
10	9.70~10.30
12	11.65~12.35
14	13.65~14.35
16	15.65~16.35
20	19.58~20.42
25	24.58~25.42
30	29.58~30.42
35	34.5~35.5
40	39.5~40.5
45	44.5~45.5
50	49.5~50.5
55	54.0~56.0
60	59.0~61.0

Thread (6g)	L	PART NO.
M2x0.4	6	RND 610-00595
	8	RND 610-00592
	10	RND 610-00593
	12	RND 610-00594
M2.5x0.45	6	RND 610-00598
	8	RND 610-00599
	10	RND 610-00596
	12	RND 610-00597
M3x0.5	5	RND 610-00600
	6	RND 610-00601
	8	RND 610-00602
M4x0.7	6	RND 610-00608
	8	RND 610-00609
	10	RND 610-00603
	25	RND 610-00604
	30	RND 610-00605
	40	RND 610-00606
50	RND 610-00607	

Thread (6g)	D Head Diameter	H Head Height	Type H Drive Size	M (Ref) Drive Width	Q Drive Depth
M1.6x0.35	2.90~3.20	1.18~1.42	0	1.80	0.72~1.02
M2x0.4	3.70~4.00	1.48~1.72	1	2.50	1.10~1.40
M2.5x0.45	4.70~5.00	1.88~2.12		2.70	1.30~1.60
M3x0.5	5.70~6.00	2.28~2.52	2	3.10	1.70~2.00
M3.5x0.6	6.64~7.00	2.58~2.82		4.20	1.74~2.24
M4x0.7	7.64~8.00	2.95~3.25		4.60	2.04~2.54
M5x0.8	9.64~10.00	3.65~3.95	3	5.30	2.77~3.27
M6x1.0	11.57~12.00	4.45~4.75		6.80	3.03~3.53
M8x1.25	15.57~16.00	5.85~6.15		4	9.00
M10x1.5	19.48~20.00	7.32~7.68	10.20		5.38~5.88

Thread(6g)	L	PART NO.
M5x0.8	10	RND 610-00610
		RND 610-00616
	12	RND 610-00611
	16	RND 610-00612
		RND 610-00617
	40	RND 610-00613
	50	RND 610-00614

