



Netac flash drives can be widely used in computers, in-vehicle devices, game consoles and other devices that have a USB interface and are compatible with this product. It can easily realize data backup, storage and transmission.



- Rotation protection

U185 Flash Drive

8GB

16GB

32GB

64GB

128GB

Highlights

- With lanyard hole
- Cap interface protection

Product Specification

Interface	USB 2.0
Dimension(mm)	57.5*19.5*8.5 mm
Net Weight(g)	About 7g
Housing material	ABS+PC
Standard color	White + black
Data transfer rate write(MB/s)	3-10MB/s
Data transfer rate read(MB/s)	12-25MB/s
operating temperature (°C)	0-60°C
Storage temperature (°C)	-20-70°C
Operation System	Windows 7/8 /10+ ;Mac OS X 10.5 +; Linux 2.6.x or +
Max Working Voltage(V)/Current(mA)	V=5V/A=150mA
Warranty period	5 years