


AS-I AND 2X AUX. POWER DISTRIBUTER FOR MASI68

MASI68 passive distribution box
2 × Aux. Power

For connection cables please see chapter "Connection Technology" All housings are fully potted

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



System connection

Communication and module supply via AS-Interface system connection

Connections

Fieldbus	M12, A-coded
I/O ports	M12, 5-pole

Technical Data

Bus voltage (AS-Interface)	26.5...31.6 V DC
----------------------------	------------------

External supply	24 V DC external (18...30.2 V DC) EN 61131-2, 2 x separately aux power
Current via M12 port	max. 4 A
Total current	max. 2 x 8 A

General data

Protection	IP68
Mounting method	2-hole screw mounting
Temperature range	-20...+60 °C (storage temperature -20...+70 °C)
Dimensions H x W x D	151x30x34.5 mm

Commercial data

country of origin	DE
customs tariff number	85176200
minimum order quantity	1