

DESINA HYBRIDFIELDBUS



PUR 2x0.34 + 4x1,5 violet 15m

Male straight to female straight
DESINA® ECOFAST®
Connection cables Han-Brid®
6-pole, CU, shielded

Further cable lengths on request. Han-Brid® a registered trademark of HARTING KGaA. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Product may differ from Image

Form

33011

Technical Data

Operating voltage	24 V AC/DC
Operating current per contact	max. 10 A
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	Clip locking

Cables

Cable number	964
No./diameter of wires	4×1.5 + 2×0.34 mm ²
Wire isolation	PVC (bk, num), (rd, gn)
Jacket Color	violet
Material (jacket)	PUR
Outer diameter	approx. 10.0 mm
Bend radius (moving)	8 × outer Ø
Temperature range (fixed)	-30...+70 °C
Temperature range (mobile)	-40...+60 °C

General data

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1