

658 Bi- and Tri-Color Series


Watertight Series Panel Mount Indicators




Dimensions

inches [mm]

Domed Lens





Certifications & Ratings

- RoHS compliant
- NEMA 4X
- IP67

Application

The 658 Series LED Panel Mount Indicators are designed with a highly durable watertight housing. These indicators are designed for a variety of applications such as:

- Electrical control panels
- Wastewater treatment controls
- Buses and transit vehicles dashboards
- Agricultural and construction equipment dashboards
- Aircraft and military vehicles dashboards
- Status Indication on industrial equipment
- ... and many more!

Mechanical Information

Mounting Hole Size: 1.000" (25.40 mm)

Max Panel Thickness: 0.350" (8.89 mm)

Mounting Torque: 15 in-lbs

Specifications

Voltage Options: 12-30 VDC (no resistor required)

Operating Temp: -40 °C to +85 °C

(-40°F to +185°F)

Storage Temp: -40 °C to +100 °C

 $(-40 \,^{\circ}\text{F to } +212 \,^{\circ}\text{F})$

Electrical

Connection: 18 AWG anti-capillary wire,

Common Cathode

Housing: Polycarbonate (UL 94V-0) **Lens Material:** Polycarbonate (UL 94V-0)

Wire Leads: 6'' — Wire color is the same color

as LED color; Black wire is

common ground

Lock Washer: White Nickel Plated Bronze


White Nickel Plated Brass

Nut: White Nickel Plated Brass





Ordering Information 658 Series



Domed

Part Number	LED Color	Lens Color	Typ. IF (mA)	Typ. VF (VDC)	Typical Intensity (mcd)
658-2415-303F	Red	White Diffused	20	12–30	1000
	Green				2100
658-2425-303F	Red				1000
	Blue				400
658-2435-303F	Green				2100
	Yellow				1000
658-2455-303F	Red				1000
	Yellow				1000
658-2465-303F	Green				2100
	Blue				400
658-2485-303F	Red				1000
	Green				2100
	Blue				400
658-2495-303F	Red				1000
	Green				2100
	Yellow				1000

Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for at: https://www.dialight.com/resources/warranties/, Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.