

## T5 Emergency F8W/T5/133/SP200 EMERGENCY LAMP 0001905



### Product features



### PRODUCT OVERVIEW

Product name	F8W/T5/133/SP200 EMERGENCY LAMP
Technology	Fluorescent
Watt (Rated) (W)	7.3
Lamp shape	Tubular shape
Type	T5 Emergency
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number Norway	3800758
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	640
CRI (Ra)	60
Wattage (W)	8.00
Product Voltage (V)	56
Dimmable	Yes
Average life (Nominal) (h)	8000
Product EAN number	5410288019055

### DATA TABLE

#### General data

Product name	F8W/T5/133/SP200 EMERGENCY LAMP
Technology	Fluorescent
Watt (Rated) (W)	7.3
Lamp shape	Tubular shape
Type	T5 Emergency
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number Norway	3800758

## T5 Emergency

*F8W/T5/133/SP200 EMERGENCY LAMP*  
0001905

### Optical data

Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	640
CRI (Ra)	60
Adjustable chromaticity	N

### Electrical data

Wattage (W)	8.00
Watt (Rated) - High frequency (W)	2.7
Current (A)	0.145
Product Voltage (V)	56
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Drive current (mA)	145

### Lifetime data

Average life (Nominal) (h)	8000
Average life (Rated) (h)	8000

### Physical data

Nominal Product Length (mm)	300.0
Nominal Product Diameter (mm)	16
Max. Length base to base (mm) - A	288.3
Length base to pin Min-Max (mm) - B	293.0-295.4
Max. Lamp Length (mm) - C/L	302.5
Max. Lamp Diameter (mm) - D	17.0
Weight (kg)	0.024

### Packaging

Single packaging type	Without Packaging
Product EAN number	5410288019055
Packaging single length / height (cm)	30.3
Packaging single width (cm)	1.6
Packaging single depth (cm)	1.6
DUN14 (outer)	15410288019052
Units per outer package	200
Packaging outer length / height (cm)	36.0
Packaging outer width (cm)	19.0
Packaging outer depth (cm)	28.0

### Safety data

Lamp mercury content (mg)	2.30
Breakage cleaning instructions	Applicable



**T5 Emergency**  
*F8W/T5/133/SP200 EMERGENCY LAMP*  
**0001905**

---

Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Suitable for household illumination	Yes