


Lumina

Lumina Pulse LED 2700K

3039980



Product features

- Ambient decorative Pulse LED cubic horizontal wall light with direct / indirect lighting to provide a soft lighting effect, 2700K amber white colour temperature, white aluminium body and integrated LED (non-dimmable) driver, 314 lumens, 6W, 52lm/W, 2700K, IP20, RAL 9003



PRODUCT OVERVIEW

| | |
|-----------------------------|-------------------------------------|
| Product name | Lumina Pulse LED 2700K |
| Technology | LED |
| Housing | Aluminium |
| Mount | Wall surface mounted |
| Environment | Internal |
| General application | Hospitality, Residential & Consumer |
| ETIM Class | EC002892 |
| E-number FI | 4271106 |
| E-number SE | 7502649 |
| Warranty | 3 years |
| Fixture luminous flux (lm) | 314 |
| Luminaire efficacy (lm/W) | 52 |
| LOR (%) | 100 |
| Colour temperature (K) | 2700 |
| Light colour | Amber White |
| CRI (Ra) | 85 |
| Total power consumption (W) | 6 |
| Electrical protection | Class II |
| Control gear type | LED driver constant current |
| Dimming method | N/A |
| Housing colour | White |
| IP rating | IP20 |
| IK rating | IK02 |
| Product EAN number | 8711971399803 |

DATA TABLE

General data

| | |
|--------------|------------------------|
| Product name | Lumina Pulse LED 2700K |
| Technology | LED |
| Housing | Aluminium |
| Mount | Wall surface mounted |

Lumina

Lumina Pulse LED 2700K

3039980

| | |
|---|-------------------------------------|
| Environment | Internal |
| General application | Hospitality, Residential & Consumer |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC002892 |
| E-number FI | 4271106 |
| E-number SE | 7502649 |
| Warranty | 3 years |

Optical data

| | |
|----------------------------|-------------|
| Fixture luminous flux (lm) | 314 |
| Luminaire efficacy (lm/W) | 52 |
| LOR (%) | 100 |
| Colour temperature (K) | 2700 |
| Light colour | Amber White |
| CRI (Ra) | 85 |
| Adjustable chromaticity | N |

Electrical data

| | |
|--|-----------------------------|
| Total power consumption (W) | 6 |
| Mains voltage (V) | 100-240V |
| Electrical protection | Class II |
| Control gear type | LED driver constant current |
| Transformer required | No |
| Dimming method | N/A |
| Drive current (mA) | 500 |
| Energy Efficiency Class (A->G) of contained light source | F |

Lifetime data

| | |
|------------------|-------|
| Lifespan L70 B50 | 50000 |
| Lifespan L80 B20 | 35000 |
| Lifespan L90 B10 | 25000 |

Physical data

| | |
|-----------------------------|-------|
| Housing colour | White |
| IP rating | IP20 |
| IK rating | IK02 |
| Nominal Product Length (mm) | 80 |
| Nominal Product Width (mm) | 138 |
| Nominal Product Height (mm) | 100 |
| Weight (kg) | 0.429 |


Packaging

| | |
|---------------------------------------|---------------|
| Single packaging type | Carton |
| Product EAN number | 8711971399803 |
| Packaging single length / height (cm) | 14.5 |
| Packaging single width (cm) | 8.5 |
| Packaging single depth (cm) | 11.07 |

Lumina Lumina Pulse LED 2700K 3039980

| | |
|--------------------------------------|----------------|
| DUN14 (outer) | 18711971399800 |
| Units per outer package | 20 |
| Packaging outer length / height (cm) | 44.5 |
| Packaging outer width (cm) | 31.0 |
| Packaging outer depth (cm) | 25.0 |

PHOTOMETRY



TECHNICAL DRAWINGS

