

Pitbull tensioning clamps

Application:

For clamping workpieces.

Execution:

- Clamp with blunt edge
- Pitbull tensioning clamps for fixture plates

Advantage:

- Space-saving, ideal for multiple clamping
- Compact design allows machining on multiple sides
- Secure clamping thanks to high clamping force
- Strong pull-down force, which enables precise machining
- Thanks to its low height, no troublesome edges for tools

Delivery:

Ref. no. 26



Art. no.	26222 308
Brand	IBT
Manufacturer Part Number	X56085
Size	8
Distance	15.2 mm
Length	38.1 mm
Width	38.1 mm
Thickness	9.5 mm
Tension force	50 kN
Width 2	16.3 mm
Material of clamping clip	Steel
Tightening torque	145 Nm
Max. clamping width	1.9 mm
Thread dimension	M12
Number of pieces in assortment/set	2 PCS
Gross Weight	0.418 kg
Product Group	278