

## Electronic torque/angle-controlled wrench 7000-2 sTAC system

SmartTAC SYSTEM 1-1000 Nm, with Bluetooth interface



### Application:

For highly precise screw connections

### Execution:

- 3-fold signalling of the screwing process via acoustic signal (buzzer), vibration and all-round 360° LED display with 'traffic-light function' visible from any position
- Measured value display in 13 mm front size, incl. a pass/fail bolting rating
- Memory: for up to 3000 measurements, incl. date and time
- Large rotation angle range (adding) up to 999°
- Effective length for other plug-in tools adjustable/programmable
- Adjustable torque units: Nm, lbf ft, lbf in, kgf m
- Variable threshold value (first warning stage)
- Programmability of parameter sets and processes
- Control function: programmable torque control on rotation angle tightening and rotation angle control on torque tightening



### Advantage:

- Large, high-contrast illuminated, easy-to-read OLED display, 180° rotatable
- Safety switch-on and switch-off function (2x button press) and automatic, time-dependent and energy-saving stand-by function
- USB socket for charging the battery directly on the tool
- Plug-in reversible ratchet included in scope of delivery

### Delivery:

Includes plug-in reversible ratchets

<b>Art. no.</b>	<b>52263 120</b>
<b>Brand</b>	HAZET
<b>Manufacturer Part Number</b>	7290-2STAC
<b>Min. torque</b>	5 Nm
<b>Max. torque</b>	60 Nm
<b>Min./max. torque</b>	5-60 Nm
<b>Torque measuring accuracy</b>	+/- 1 %
<b>Tip size</b>	3/8 inch
<b>Insert shank square</b>	9 x 12 mm
<b>Length</b>	302 mm
<b>Error limit (%)</b>	1 %
<b>Gross Weight</b>	3.700 kg
<b>Product Group</b>	569

### EAN

4000896223169