

## pneumatic spiral hose

With eSafe safety coupling



### Application:

for connection to compressed-air tools and compressed-air machines.

### Execution:

- With eSafe safety coupling and nipple
- ends and rotary joint axially offset on both sides
- max. pressure: 10 bar

### Advantage:

- Coupling and nipple (DN 7.6) pre-installed for immediate use
- Lightweight and flexible
- Long life with excellent ageing properties
- The ventilation function of the eSafe safety coupling reduces the noise level and prevents accidents caused by the whiplash effect



<b>Art. no.</b>	<b>75055 011</b>
<b>Brand</b>	CEJN
<b>Manufacturer Part Number</b>	19 958 9763
<b>Hose length</b>	2 m
<b>Outer diameter of hose</b>	10 mm
<b>Inner hose diameter</b>	6.5 mm
<b>Max. operating pressure</b>	10 bar
<b>Gross Weight</b>	0.328 kg
<b>Product Group</b>	7AI

### EAN

7391390097330