

# DL50/740 PX32d 1CT

Product family description  
 35 and 50W microdischarge lamps with a 4.2 mm arc length mounted on a P32-d base

**Product Features**

- Lamp voltage approx. 85 V
- Characteristic life (Tc) 5000 h (DL35/745) or 3000 h (DL50)
- Burning position horizontal  $\pm 10^\circ$

**Product Benefits**

- Very low UV emission due to UV-Block outer bulb
- Can withstand 'fast run-up' mode as used in automotive applications
- Hot restrike capability (ballast must have sufficient starting voltage and power)

**Application**

- Medical applications
- Torches
- Working lights
- Fibre optics

**Luminaires**


- Must be used in closed luminaires only

**System**


- Can only be used with an electronic ballast and starter

Product data	
Order code	439321 30
Full product code	871150043932130
loccod	
Full product name	DL50/740 PX32d 1CT
Order product name	DL50/740 PX32d 1CT/24
Packing type	1 Carton
Pieces per pack	1


Product data	
Packing configuration	24
Packs per outerbox	24
Bar code on pack - EAN1	8711500439321
Bar code on intermediate packing - EAN2	
Bar code on outerbox - EAN3	8711500439345
Logistic code(s) - 12NC	9285 500 29404
ILCOS code	
Net weight per piece	20.780 GR
Successor order code	
Philips Code	DL50/740
Cap-Base	PX32d
Technical Type	50



XDMDP 50 PX32d



XDMDP P32d/PX32d



Burning Position p10

