

PeakTech® 1640



- ▶ 3 3/4-stellige, 17 mm LCD-Anzeige; max. Anzeige: 3999
- ▶ Echt-Effektivwertmessung
- ▶ Automatische und manuelle Bereichswahl
- ▶ Messwerthaltefunktion
- ▶ Hintergrundbeleuchtung
- ▶ AC/DC-Leistung: 240 kW
- ▶ AC/DC-Strom: 1000 A
- ▶ Spannungsmessung bis 600 V AC/DC
- ▶ Widerstands- und Frequenzmessfunktion
- ▶ Diodentest und Durchgangsprüffunktion
- ▶ Abschaltautomatik
- ▶ Leiterdurchmesser: 35 mm max.
- ▶ Sicherheit: EN 61010-1; CAT III 600 V
- ▶ Zubehör: Tasche, Prüfleitungen, Batterie und Bedienungsanleitung



- ▶ 3 3/4 digit, 17 mm LCD; max. indication: 3999
- ▶ True RMS
- ▶ Auto/manual range selection
- ▶ Data hold
- ▶ Backlight
- ▶ AC/DC power: 240 kW
- ▶ AC/DC current: 1000 A
- ▶ AC/DC voltage: 600 V
- ▶ Resistance- and frequency measurement
- ▶ Diode test and continuity test
- ▶ Auto power off
- ▶ Max. conductor size: 35 mm
- ▶ Safety: EN 61010-1; CAT III 600 V
- ▶ Accessories: carrying case, test leads, battery and manual

PeakTech® 1645



- ▶ 3 2/3-stellige, 11 mm LCD-Anzeige; max. Anzeige: 2000, 32 Segment analoge Balkengrafik
- ▶ AC/DC-Strom: 200 A
- ▶ AC/DC-Spannung 600 V, Widerstand und Durchgangsprüfung
- ▶ Echteffektivwert-Messung
- ▶ Messwerthaltefunktion
- ▶ Min/Max- und DCA-Nullabgleich-Funktion
- ▶ Maximalwerthaltefunktion
- ▶ Spitzenwerthaltefunktion
- ▶ Hintergrundbeleuchtung
- ▶ Berührungsloser Spannungsdetektor 100 - 600 V AC und Taschenlampe
- ▶ Abschaltautomatik
- ▶ Batteriezustandsanzeige
- ▶ Leiterdurchmesser: 18 mm max.
- ▶ Sicherheit: EN 61010-1; CAT III 600 V
- ▶ Zubehör: Prüfleitungen, Tasche, Batterien und Bedienungsanleitung

- ▶ 3 2/3 digit, 11 mm LCD; max. indication: 2000, 32 segment analogue bargraph
- ▶ AC/DC current: 200 A
- ▶ AC/DC voltage 600 V, resistance and continuity check
- ▶ True RMS
- ▶ Data hold
- ▶ Min/Max- and DCA zero function
- ▶ Peak hold function
- ▶ Max hold function
- ▶ Backlight
- ▶ Non-contact voltage detector 100 - 600 V AC and flashlight
- ▶ AC/DC current: 200 A
- ▶ Auto power off
- ▶ Low battery indication
- ▶ Max. conductor size: 18 mm
- ▶ Safety: EN 61010-1; CAT III 600 V
- ▶ Accessories: test leads, carrying case, batteries and operation manual