



# RegLED CCT

REGLED CCT 18W 1473MM I

Reglette LED downlight with variable light colour warm, white, cold

**Order code 74079**

**EAN 8002219743893**

## Technical specifications

Absorbed Power	<b>16.5 W</b>
Supply voltage type	<b>AC</b>
Nominal voltage (AC)	<b>230 Vac</b>
Ambient temperature (min)	<b>-20 °C</b>
Ambient temperature (max)	<b>40 °C</b>
Insulation class	<b>II</b>
CCT light tone	<b>3000 K, 4000 K, 5000 K</b>
Colour consistency	<b>SDCM3</b>
CRI color rendering	<b>&gt;80</b>
Ballast	<b>For constant current LED</b>
Efficiency	<b>93 lm/W</b>
Frequency (max)	<b>60 Hz</b>
Frequency (min)	<b>50 Hz</b>
Glow wire strength	<b>850 °C - 30s.</b>
MTBF driver	<b>30000 h</b>
Luminaire flux	<b>1530 lm</b>
Voltage supply range (max)	<b>265 V</b>
Voltage supply range (min)	<b>180 V</b>

## Installation and applications


Environment	<b>Offices</b>
Application	<b>Shelves, Shops</b>

## Mechanical specifications


Height	<b>30 mm</b>
Length	<b>1473 mm</b>
Width	<b>22 mm</b>
Weight	<b>0.28 Kg</b>
Colour housing	<b>White</b>
Protection grade IP	<b>IP20</b>
Protection grade IK	<b>IK05</b>

## Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN IEC 60598-1:2021, EN 60598-2-1:1989, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013



N° max moduli in serie 10



## Supplied accessories



**424020003**  
CONNECTION PLUG 150 RGL  
LEDECO



**424020004**  
GR ACCESSORY RGL LEDECO



**424020006**  
MAIN POWER L1500 REGLED  
ECO

## Accessories



**424020005**  
CONN PLUG 1.5MT RGL  
LEDECO



**424020009**  
CONNECTION PLUG 2MT RGL  
LEDECO