


E20511



Fibre optic diffuse reflection sensor

FT-00-MPV-M6



Application	
Function principle	Diffuse reflection sensor
Detection zone	
Range with fibre optic amplifier type	OKF; OUF; OOF
OKF	
Range fibre optics [mm]	20
OOF	
Range fibre optics [mm]	220
OUF	
Range fibre optics [mm]	20
Operating conditions	
Ambient temperature [°C]	-20...80

E20511



Fibre optic diffuse reflection sensor

FT-00-MPV-M6

Mechanical data	
Weight [g]	58.5
Version of sensing head	straight
Sensing head thread	M6
Sensing head diameter [mm]	7
Sensing head length [mm]	45
Total length [mm]	600
Min. bending radius [mm]	20
Fibre arrangement	
Fibre material	PMMA
Fibre head material	stainless steel (1.4305 / 303)
Fibre sheath material	metal silicone
Accessories	
Accessories (supplied)	hexagon nuts: 4 x M6, stainless steel
	tooth lock washers: 2
	knurled nut: 1 x M11
Remarks	
Pack quantity	1 pcs.