








# **Model Number**

NCN25-30GM50-Z4

## **Features**

- 25 mm not embeddable
- 2-wire DC
- Increased operating distance

## Connection




#### **Accessories**

BF 30

Mounting flange, 30 mm

## **Dimensions**



# **Technical Data**

General specifications						
	Switching element function		DC	NO		
	Rated operating distance	s <sub>n</sub>	25 mm			
	Installation		not embed	dable		
	Output polarity		DC			
	Assured operating distance	sa	0 20 mn	า		
	Reduction factor r <sub>Al</sub>		0.4			
	Reduction factor r <sub>Cu</sub>		0.4			
	Reduction factor r <sub>303</sub>		0.7			
	Reduction factor r <sub>Brass</sub>		0.5			

Nominal ratings					
Operating voltage	U <sub>B</sub>	3.5 30 V			
Switching frequency	f	500 Hz			
Hysteresis	Н	typ. 3 %			
Reverse polarity protected		reverse polarity-conductive			
Short-circuit protection		pulsing			
Voltage drop	$U_d$	≤ 3.5 V			
Temperature drift		± 15%			
Operating current	ΙL	2 100 mA			
Off-state current	l <sub>r</sub>	typ. 0.8 mA			
Indication of the switching state		LED, yellow			
Pre-fault indication		LED, red			
Stability control-switch point		0,8 s <sub>r</sub> 0,9 s <sub>r</sub>			
Ambient conditions					

# Ambient conditions

-25 ... 70 °C (-13 ... 158 °F) -25 ... 85 °C (-13 ... 185 °F) Ambient temperature Storage temperature

#### Mechanical specifications

Connection type Core cross-section cable PVC , 2 m  $0.34~\text{mm}^2$ brass, nickel-plated Housing material PBT Sensing face Protection degree IP67

## Compliance with standards and directives


#### Standard conformity

EN 60947-5-2:2007 Standards IEC 60947-5-2:2007


#### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Products with a maximum operating voltage of ≤36 V do not bear a

www.pepperl-fuchs.com



Correlation between output signal/LED-function and stable operating distance s<sub>s</sub>/ effective operating distance  $s_r$ : ( $s_s$  typ. 80 % of  $s_r$ )



FPEPPERL+FUCHS