

811.1023

**M** Pliers, hammer and chisel set



568 x 398



P10



P10TC



P15



P20



P30




P35



P45



Pos.	Code	Description	pcs
1	156.0236	Pin punch, Ø 2 mm, cylindrical shaft	1
2	156.0231	Pin punch, Ø 3 mm, cylindrical shaft	1
3	156.0232	Pin punch, Ø 4 mm, cylindrical shaft	1
4	156.0233	Pin punch, Ø 5 mm, cylindrical shaft	1
5	156.0234	Pin punch, Ø 6 mm, cylindrical shaft	1
6	156.0235	Pin punch, Ø 8 mm, cylindrical shaft	1
7	156.0253	Flat chisel, octagon, 16 mm	1
8	156.0254	Flat chisel, octagon, 18 mm	1
9	156.0243	Centre punch, octagon 10 mm	1
10	156.0242	Cross chisel, octagon, 7 mm	1
11	115.1012	ERGOTORQUE diagonal side cutter, 160 mm	1
12	115.1021	ERGOTORQUE combination pliers, 180 mm	1
13	115.1024	ERGOTORQUE long nose pliers serrated cutter, 200 mm	1
14	115.1231	Multifunction pliers for insulated and non insulated cable terminals, 220 mm	1
15	115.1033	Self grip wrench, 220 mm	1
16	115.2010	Water pump pliers, 240 mm	1
17	115.1239	Self regulating wire stripper, 0,2 - 6 mm	1
18	500.1029	Circlip pliers for external circlips, 160 mm	1
19	907.2232	Gasket scraper, 25 x 200 mm	1
20	201.2320	Steel wire brake saddle wire brush 2 rowed, straight	1
21	142.1402	Fitters hammer, fibreglas handle, 400 g	1
22	140.5252	Recoil free soft faced hammer, 400 g	1
23	911.8138	Trim plastic wedge, 195 x 30mm	1



P 10

P 15

P 20

P 25

P 30

P 35

P 40

P 45

M

L

S

XL

Individual parts

Accessories