# Product data sheet Characteristics

# XZCC20FCM30B

female, 1/2 20UNF, 3-pin, elbowed connector - cable gland Pg 7



abling accessories
onnector
lbowed female connector 1/2 20 UNF, 3 pins
letal
/ithout
crew terminal 0.00 in² (0.75 mm²) 0.120.24 in 36 mm)
1

### Complementary

Pg 7	
Screw-on	
250 V AC	
4 A	
Plastic	
1000 GΩ	
8000 μOhm	
0.04 lb(US) (0.02 kg)	
	Screw-on 250 V AC 4 A Plastic 1000 GΩ 8000 μOhm

### **Environment**

2.171.011.101.1	
IP degree of protection	IP67
Ambient air temperature for operation	-40185 °F (-4085 °C)

# Ordering and shipping details

Category	22483 - MACHINE CABLES
Discount Schedule	DS3
GTIN	00785901400493
Nbr. of units in pkg.	1
Package weight(Lbs)	0.06 lb(US) (0.03 kg)
Returnability	No
Country of origin	CZ

## **Packing Units**

Package 1 Height	0.200 dm	
Package 1 width	0.360 dm	
Package 1 Length	0.400 dm	

### Offer Sustainability


California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☐ REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS  Declaration
Mercury free	Yes
RoHS exemption information	₫Yes

Warranty	18 months

# Product data sheet Dimensions Drawings

# XZCC20FCM30B

## **Dimensions**



(1) Cable gland : no. 7 plastic (Pg 7)

# Product data sheet Connections and Schema

# XZCC20FCM30B

## Connections and Schemes

