

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202530396](#)
Status: **Active**
Overview: Contrinex Inductive and Photoelectric
Description: Contrinex Inductive Sensor, M18 Housing, 8mm Operating Distance, Embeddable, PNP, NO, 4-pin M12 Connector, 63.5mm Housing Length

Documents:

[Product Specification 1202530396-000 \(PDF\)](#)

[Product Literature \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Sensors
Series	120253
Exclude SD Check	Yes
IP Rating	IP67
Overview	Contrinex Inductive and Photoelectric
Product Category	Sensors
Product Literature Order No	987651-9402
Product Name	Contrinex
Type	Inductive
UPC	191130066612

Physical

Connection	Connector (M12, 4-pin)
Length	63.50mm
Material - Housing	Nickel Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Embeddable
Operating Distance	8mm
Output	NO
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +70°C

Electrical

Polarity	PNP
Switching Frequency	≤ 1500 Hz

Material Info

Engineering Number	DW-AS-623-M18-002
--------------------	-------------------

Reference - Drawing Numbers

Product Specification	1202530396-000
-----------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120253 Series](#)