

12PCS SET WITH 50MM BIT SLEEVE E.612 AND 4V E-PROTWIST HANDLE



Description:

- 4V E-Protwist handle.
- Speed: drives screws up to 4x faster vs a manual screwdriver.
- More efficiently, healthier approach to work.
- 300 Rpm for high speed screw fastening up to 0,9Nm.
- Provides reduced fatigue in low torque applications.
- Compact tool to transport easily.
- E-Protwist is portable and can be used easily.
- Electric screwdriver take less space to operate.
- Bi-material handle and protwist ergonomic design.
- Fast charging (UCB-C) ; 70 min-saves your precious time.
- 3-stage LED battery charge indicator (green – amber – red).
- 5 bulb LED workspace illumination.
- Forward & reverse push buttons.
- Quick change solution for bits.
- IP 54 rating for advanced water and chemical resistance.
- E.612 SET OF 10 BITS 50 MM LONG WITH GROOVE
- Drive 1/4" - 6.35 mm.
- Including:
 - - 3 bits for Phillips® screws: EP.601T - EP.602T (x2).
 - - 3 bits for Pozidriv®: ED.601T - ED.602T (x2).
 - - 4 Torx® bits: T10 - T20 - T25 - T30.

- Supplied in compact high strength and chemical resistant polyamide case.

	Length L [mm]	Diameter [mm]	Weight [kg]	Connection [in]
ATPA4V.J12APB	170	36	0.671	1/4