



PCB Layout
(Top View)

Dimensions			
Pos.	A	B	C
10	32.00	21.84	10.16
14	37.08	26.92	15.24
16	39.62	29.46	17.78
20	44.70	34.54	22.86
24	49.78	39.62	27.94
26	52.32	42.16	30.48
30	57.40	47.24	35.56
34	62.48	52.32	40.64
40	70.10	59.94	48.26
50	82.80	72.64	60.96

RoHS
Compliant

HSM 玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

Material and Finish	Electrical Characteristics	Mechanical Characteristics
1. Housing: Thermoplastic (UL94V-0), Black. 2. Terminal: Sq. 0.64mm, Gold Plating.	1. Current Rating: 3.0 Amp. Max. 2. Dielectric Withstand Voltage: 1000V AC RMS for 60Seconds. 3. Insulation Resistance: 1000M Ohms Min. at 1000V DC.	1. Operating Temperature: -55°C ~ +105°C

APPD. 核准 Ivy	 SCALE 比例 参考	TOLERANCE 容許公差 0.0 ±0.30 0.00 ±0.20 0.000 ±0.10
DWG. 製圖 Jolin		UNIT 單位 M M
DATE 制表日 2006/10/25	PAGE 張數 1 OF 1	SIZE 紙張尺寸 A 4
		REV. 版本 A

PART NAME 品名 FULLY SHROUDED HEADER ASSEMBLY 2.54mm X 2.54mm 10P SHORT LOCK90° GOLD PLATING BLACK COLOR ROHS LOW-LEAD
PART NO. 料號 C3000-XXRSGB00R