




DIN 985

Standard withdrawn



BN 637

Prevailing torque type hex lock nuts

thin type, with polyamide insert

Stainless steel A2

- ~UNI 7474

M2,5: not included in DIN 985, M10; M12; M14; M22: wrench size according to ISO on request

Article#	d ₁	e min.	h max.	m	s
1143735	M2,5	5,51	3,8	2	5
1242377	M3	6,01	4	2,4	5,5
1242385	M4	7,66	5	2,9	7
1242393	M5	8,79	5	3,2	8
1242407	M6	11,05	6	4	10
1242415	M8	14,38	8	5,5	13
1242423	M10	18,9	10	6,5	17
1242431	M12	21,1	12	8	19
1169998	M14	24,49	14	9,5	22
1242458	M16	26,75	16	10,5	24
8195706	M18	29,56	18,5	13	27
1242466	M20	32,95	20	14	30
8303355	M22	35,03	22	15	32
1242474	M24	39,55	24	15	36
5402518	M27	45,2	27	17	41
5402519	M30	50,85	30	19	46