

---

## ORIGINAL

Lamps with metal bases



---

### Areas of application

- Position and parking light
- Indicator, brake, fog and reversing lights
- Number plate and side position lights

---

### Product benefits


- OEM Quality
- Wide product range
- Reliable quality

---


### Product features

- Original spare parts


# Product family datasheet




Product line drawing




Product line drawing




Product line drawing




Product line drawing




Product line drawing



Product line drawing



Product line drawing



Product line drawing

## Product family datasheet

### Technical data

Product description	Electrical data					Photometrical data		Dimensions & weight
	Power input	Nominal voltage	Nominal wattage	Power input tolerance	Test voltage	Luminous flux	Luminous flux tolerance	Length
3797	3 W	24.0 V	2.00 W	±15 %	28.0 V	17.5 lm	±30 %	23.9 mm
64138	28 W	24.0 V	21.00 W	±5 %	28.0 V	600 lm	±15 %	38.9 mm
7537	28 / 10 W	24.0 V	21/5 W	±6 / ±10 %	28.0 V	440/40 lm	±15 / ±20 %	52.5 mm
7511	28 W	24.0 V	21.00 W	±6 %	28.0 V	460 lm	±15 %	52.5 mm
5637	12.5 W	24.0 V	10.00 W	±10 %	28.0 V	125 lm	±20 %	37.5 mm
5626	7 W	24.0 V	5.00 W	±10 %	28.0 V	50 lm	±25 %	37.5 mm
5627	7 W	24.0 V	5.00 W	±10 %	28.0 V	50 lm	±20 %	37.5 mm
3930	5 W	24.0 V	4.00 W	±10 %	28.0 V	35 lm	±20 %	27.4 mm
7529	15 W	24.0 V	15.00 W	±10 %	28.0 V	210 lm	±25 %	46.5 mm

Product description	Diameter	Lifespan		Additional product data	Certificates & standards	Country specific categorizations
		Lifespan B3	Lifespan Tc	Base (standard designation)	ECE category	Order reference
3797	9 mm	1000 h	2000 h	BA9s	-	3797 2W 24V BA9
64138	9 mm	150 h	400 h	BAY9s	H21W	64138 21W 24V B
7537	27.0 mm	65 / 600 h	600 / 1600 h	BAY15d	P21/5W	7537 21/5W 24V
7511	26.5 mm	200 h	400 h	BA15s	P21W	7511 21W 24V BA
5637	16.0 mm	400 h	800 h	BA15s	R10W	5637 10W 24V BA
5626	16.0 mm	80 h	250 h	BA15d	R5W	5626 5W 24V BA1
5627	16.0 mm	500 h	1000 h	BA15s	R5W	5627 5W 24V BA1
3930	8.8 mm	550 h	1000 h	BA9s	T4W	3930 4W 24V BA9
7529	25.0 mm	100 h	300 h	BA15s	-	7529 15W 24V BA

## Product family datasheet

---

### Application advice

For more detailed application information and graphics please see product datasheet.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.