



Specifications:

Dielectric Strength	500 VAC (50/60Hz) for 1 minute
Insulation Resistance	100MΩ Min. at 500 VDC
Contact Resistance	30MΩ Max. (Between Terminals) 20MΩ Max. (Switch Part)
Mechanical	0.4kg to 3.0kg (Insertion Force) 0.4kg to 3.0kg (Extraction Force)
Life Test	5,000 cycles of insertion and extraction at a rate 25 to 30 cycles per minute