

# F28WW-E

## 28° WWELD STICK NAILER-ST +CASE



Diameter: 2.8 - 3.3mm  
Length: 50 - 90mm

### Features



Rubber Comfort Grip



Magnesium Housing



Serrated Tip



No-Mar-Tip



Dial-A-Depth



Push Button Depth Control



Sequential Trip



Anti Slip Bumpers



Compact Nose



Carry Case



### SPECIFICATION

Power type	Pneumatic	Operating pressure	4.80 - 8.30 BAR
Weight	3.50 kg		70.00 - 120.00 PSI
Width	133 mm	Air Consumption Ltr.per shot @ 5.6 bar	2.47
Length	508 mm	Air fitting thread type	1/4 BSP
Height	355 mm	Noise	<b>LPA 1sd</b> 96.30
Magazine capacity (max)	90		<b>LWA 1sd</b> 100.10
WW Series Fasteners:			<b>LPA 1s, 1m</b> 87.10
Diameter (mm)	2.8 (min)      3.3 (max)	Vibration / Uncertainty	2.47 / N/A m/s <sup>2</sup>
Length (mm)	50 (min)      90 (max)		
Head (mm)	7.5 (min)      7.5 (max)		
Collation type	wire_weld		
Collation angle	28		