



Part no.: 50111226
KB M12A-8P-PC-IO-3000
Connection cable

Contents

- Technical data
- Electrical connection

Technical data

Basic data

Suitable for	LSIS 222 series stationary 2D-code readers
Suitable for interface	RS 232

Connection

Connection 1

Type of connection	Sub-D
Type	Female
No. of pins	9 -pin
Design	Axial

Connection 2

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Design	Axial

Connection 3

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Cable properties

Number of conductors	8 Piece(s)
Sheathing color	Black
Shielded	Yes
Cable design	Interconnection cable
Cable diameter (external)	6 mm
Cable length	3,000 mm
Sheathing material	PUR

Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection

Connection 1	
Type of connection	Sub-D
Type	Female
No. of pins	9 -pin

Part no.: 50111226 – KB M12A-8P-PC-IO-3000 – Connection cable

Connection 1	
Design	Axial

Connection 2	
Type of connection	Connector
Thread size	M12
Type	Female
Handle body material	
No. of pins	8 -pin
Encoding	A-coded
Design	Axial
Lock	

Connection 3	
Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial