




PIN OUT



NOTE:

1. Fluke Channel Test ISO 11801 channel Class Ea
2. RoHS2.0 AND REACH compliant
3. Electrical test: 100% open short & miss wire test;
4. OPERATING TEMPERATURE: -10°C ~ 60°C
5. Print word: CAT6A U/FTP 4x2x32AWG/7 LSZH ISO11801 & EN50173 & ANSI/TIA568C.2

ITEM No.	LENGTH
21.15.1700	500 ± 30mm
21.15.1701	1000 ± 30mm
21.15.1704	1500 ± 50mm
21.15.1702	2000 ± 50mm
21.15.1703	3000 ± 70mm
21.15.1705	5000 ± 70mm



MATERIAL LIST

③	CABLE	CAT. 6A U/FTP CABLE (32AWG BC*1P+AL-FOIL)*4 +DRAIN+JACKET:LSZH/White, OD:3.6±0.2mm	1	
②	Over mold	48P PVC/White	2	
①	Plug	RJ45 8P8C Short Shielded Plug, PIN GOLD PLATED 3u", The Shell Nickel plating, TRANSPARENT	2	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

DESC.	ROLINE Cat. 6A U/FTP Patch Cord, LSOH, Slim, White
-------	--

		NEW		2018-09-12	A
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.

SECOMP