



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG		


REVISIONS		DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398						
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1876	Α	RELEASED	EO	07/25/06	SA	07/25/06	но	07/25/06








P.C.B. LAYOUT





SPECIFICATIONS:

- 1. Shell: Steel, Tin-Plated
- 2. Contact: Brass, Stamped Pin Gold-Plated
- 3. Insulator: PBT & Fiber-Glass Reinforced UL94V-0
- 4. Current Rating: 5 Amps
- 5. Dielectric Strength: 1000 V for One Minute
- 6. Insulator Resistance: 1000 Megohms Min.

at 500V DC

REV

7. Temperature: -50°C to +105°C

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES: Unless Otherwise Specified .X ±0.2 [0.008] .XX ±0.12 [0.005]

DRAWN BY:	DATE:
EKLAS ODISH	07/25/06
CHECKED BY:	DATE:
SAMI ALNADI	07/25/06
APPROVED BY:	DATE:
HISHAM ODISH	07/25/06

Y:	DATE:	
DISH	07/25/06	
BY:	DATE:	T
NADI	07/25/06	
D BY:	DATE:	H
UDICH	07/25/06	

DRAWING TITLE: 25 Pin R/A PCB Mount D-Sub Socket

CIZE	DWO NO		EL EO	TDONIO EII	_		_
SIZE	DWG. NO.			TRONIC FIL	L		RI
Α	SPC15340			K4932.	DW	G	A
SCALE	: NTS	U.O.M.: mm [INCHES]		SHEET:	1	OF	1