

## General Information

Extended Product Type:	OHB65J6
Product ID:	1SCA022380R9660
EAN:	6417019124117
Catalog Description:	OHB65J6 Handle
Long Description:	For front operated switches. Indication in types OHB_ and OHY_ : I-O/ON-OFF, in types OHG_ : I-O. IP 65, NEMA 1,3R, 12, padlockable with three padlocks in OFF-position, door interlock in ON-position (defeatable to allow authorized personnel access for inspection). The shaft has to be ordered separately. Screw fixing from back side of the handle. No screws on the front ensures double insulation.

## Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

## Ordering

EAN:	6417019124117
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85381000

## Dimensions

Product Net Width:	98 mm
Product Net Height:	66 mm
Product Net Length:	100 mm
Product Net Depth:	45 mm
Product Net Weight:	0.12 kg

## Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	70 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	100 mm
Package Level 1 Gross Weight:	0.12 kg
Package Level 1 EAN:	6417019124117

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

## Additional Information

Color:	Black
Degree of Protection:	IP65
Handle Length:	65 mm
Handle Type:	Pistol
Order Multiple:	10 piece
Product Main Type:	OHB 65J6
Product Name:	Handle
Product Type:	OHB
Special Functions:	J6
Suitable For:	OT90A...160_
Suitable for Product Class:	Switch disconnectors

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
RoHS Information:	1SCC390010D0201

## Classifications

E-nummer:	3171400
ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

