

## GOP Boxes



### **GOP Boxes (MGOP2, MGOP4, MGOP6)**

Our range of grid outlet position boxes and latch plates are ideal for fitting onto the end of a flexible conduit. These boxes allow the presentation of 6C size outlets in a vertical grid formation, providing both cable and outlet containment within raised floor systems. They are also ideal for attaching to the underside of desks in general office environments.

### **Features**

- Available in 3 vertical grid layout options:- 2 outlets, 4 outlets and 6 outlets
- Keyed gland entry for either 25 or 32 mm flexible conduit
- Latch Plates optional - available in 25 and 32 mm sizes
- Cut out apertures are 6C (aka LJ6C) size
- 60 mm deep boxes to accommodate cable bend radius requirements
- Supplied and fitted with M6 screws for fast removal of the lid
- Suitable for use with our range of 6C fibre modules, Category 6/6A copper modules, keystone adaptors (for a wide range of connectors) and blanks  
[http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=294](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=294)  
[http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=53](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=53)  
[http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=301](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=301)

**NOTE:** GOP (Grid Outlet Position) boxes are also known as POD boxes by other manufacturers and suppliers.

### **Specifications**

- Colour: black
- Material: Cold rolled steel
- Sizes:
  - 2 outlet 138 x 60 x 63 mm
  - 4 outlet 175 x 60 x 63 mm
  - 6 outlet 225 x 60 x 63 mm

## Latch Plates



Latch Plates (MGOPLP25, MGOPLP32)

Our two Latch Plates are designed to accommodate flexible conduit during the fixing of GOP boxes into a raised floor box or in a workplace (such as under desk).

### ***Features***





- Fixing brackets for conduit used with GOP Boxes
- Available with apertures for 25 mm or 32 mm conduit
- Attractive semi-gloss finish matches our GOP boxes

### ***Specifications***


- Dimensions: 67.5 x 50 x 50 mm
- Weight: 56g
- Colour: Black
- Material: Cold rolled steel

ROHS Compliant

Code: MGOP2







Cold-rolled steel sheets: 1.5mm




ROHS Compliant

Code: MGOP4







Cold-rolled steel sheets: 1.5mm




ROHS Compliant

Code: MGOP6





Cold-rolled steel sheets: 1.5mm



ROHS Compliant

Code: **MGOPLP32**  
**MGOPLP25**



Cold-rolled steel sheets: 1.5mm