

Han 24B Protect Cover with latch Thermop



Part number	09 30 024 5401
Specification	Han 24B Protect Cover with latch Thermop
HARTING eCatalogue	https://b2b.harting.com/09300245401

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of accessory	Protection cover
Description of the accessory	for hoods Thermoplastic With board locks

Version

Size	24 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained



Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals DNV GL

Commercial data

Packaging size	1
Net weight	29.35 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140047907
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors