

Nuts

For T-grooves




Application:

For clamping in T-grooves.

Version:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form

Art. no.	26195 050
Type	standard
Nominal dimension of groove	14 mm
Slot nut width	13.7 mm
Thread dimension	M12
Length	22 mm
Height	16 mm
Slot nut height	8 mm
DIN	508



EAN-Code

4020772080044