

Grinding and control vice OP-S

Actuation via hexagon socket key

ORION[®]

Application:


For horizontal, vertical and lateral grinding, inspection and eroding tasks.

Execution:

- Made of alloyed tool steel.
- Hardened and precision-ground.
- Quick adjustment.
- Horizontally ground vee block.
- Perpendicularity tolerance 0.005 mm/100 mm (base surface to fixed jaw clamping surfaces).
- Parallelism tolerance 0.005 mm/100 mm (base surface to upper guide plate).

Delivery:

1x grinding and control vice OP-S; incl. Hexagon socket wrench



Art. no.	28600 310
Brand	ORION
Manufacturer Part Number	28600310
Prism countersunk horizontally	Yes
Jaws width	36 mm
Jaws height	20 mm
Clamping width	40 mm
Height	48 mm
Base body length	105 mm
Base body width	36 mm
Base body height	28 mm
Gross Weight	0.900 kg
Product Group	282

EAN

4053625621293