

Hinged-door cabinet with doors with viewing window, width 1200 mm

With shelves

Application:

For secure and clearly-visible storage of tools, accessories, files or many other parts.

Execution:

- Stable welded steel sheet structure with base
- With doors with viewing window with shatter-proof acrylic glass
- zinc-plated shelves, height-adjustable in increments of 17 mm, load capacity per shelf 80 kg with evenly distributed weight
- Inset-type doors with internal pivot pins, doors internally reinforced by box profile, double-edged on all sides
- locks by means of a turning handle with integrated cylinder lock, includes 3 keys 2 keys

Delivery:

Shelves with load capacity of 100 kg with evenly distributed load, DOM locking system (fits HK tool cabinets, HK tool shelves, HK workbenches) and other colours available upon request.



| | |
|---|--|
| Art. no. | 50045 225 |
| Brand | PAVOY |
| Manufacturer Part Number | 3 1310-120-590 |
| Door design | Inspection glass |
| Width | 1200 mm |
| Depth | 500 mm |
| Height | 1950 mm |
| Number of shelves | 4 PCS |
| Load-carrying capacity per shelf | 80 kg |
| Load-carrying capacity | 400 kg |
| With partition wall | No |
| Central locking | Yes |
| Lock type | Twist-grip lock with three-point fastening |
| Material | Sheet steel |
| Cabinet colour | Light grey RAL 7035 |
| Colour of front | Gentian blue RAL 5010 |
| Surface | Powder-coated |
| Gross Weight | 77.000 kg |
| Product Group | 5CB |