

Platform trolley series 500 base platform, zinc plated

Loading area made of MDF board, load capacity 500 kg



Execution:

- Galvanised
- Loading area height 260 mm
- 2 fixed castors and 2 castors made of solid rubber 200 x 50 mm
- Loading area made of melamine-coated MDF board
- 2 fixed castors and 2 castors made of solid rubber 200 x 50 mm
- The 500 series also includes table trolleys, cabinet trolleys, platform trolleys with front walls and other variants.



Art. no.	50250 011
Brand	KONGAMEK
Manufacturer Part Number	KM530-2B
Type	Platform
Load-carrying capacity	500 kg
Length	1000 mm
Width	700 mm
Height	260 mm
Loading surface length	1000 mm
Loading surface size	1000 x 700 mm
Loading-surface width	700 mm
Material of loading surface	Medium density fibreboard
Colour	Silver coloured
Surface	Zinc plated
Number of steering rollers	2
Number of fixed rollers	2
With wheel lock	Yes
Wheel diameter	200 mm
Material of wheel	Solid rubber
Gross Weight	23.500 kg
Product Group	5AT

EAN

7350050357573